



4587

**FCC soc. out. 8/8pole shielded, cat.6 iso, com-tech**

### Technical properties

#### Architecture

Design to according to DIN EN 60603-7-51

#### Connectivity

Outlet with 45° oblique outlet

Plug type for RJ11, RJ12 and RJ45 plugs

#### Main electrical features

Rated voltage 72 V DC

Rated current 1 A

#### Voltage

Voltage suitable for PoE+

#### Electric current

Rated current 1 A

#### Dimensions

Insertion depth 31 mm

#### Frequency

Transmission bandwidth max. 500 MHz

#### Resistance

Shield contact resistance 100 mΩ

Signal contact resistance 20 mΩ

#### Materials

Colour code A and B according to TIA/EIA-568-B.2

Material / surface Housing made of die-cast zinc

#### Installation, mounting

Installation mode without spreader claws, screw fastening via supporting plate

#### Connection

Type of connection with LSA + terminals

Contact with screen contacting 360° and strain relief

#### Cable

Conductor Ø 0.4...0.63 mm

Wire flexible cable routing

**Equipment**

---

Supporting plate / Supporting ring external eyelets on the supporting ring can be broken off for round designs

**Safety**

---

Cat.6<sub>iso</sub>, Class E<sub>A</sub>, shielded according to ISO/IEC 11801 A2

Protective screen according to DIN EN 55022, Class B

Protection index IP IP20

Protection No

**Use conditions**

---

Operating temperature -40...70 °C

**Identification**

---

Application, usage Communication technology

Main design line Communication technology