



47088982

**SCHUKO soc.out. residual current circuit-breaker,enhncd contact prot.,S.1,wh.gl.**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting
Type	type A for alternating currents and pulsating direct currents

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Measurement error current	30 mA
Rated current	16 A
Surge current resistance	250 A (8/20) $\mu$ s
Short-circuit resistance (with back-up fuse 20 AgL)	3 kA

**Dimensions**

Insertion depth	31.9 mm
-----------------	---------

**Tripping**

Trigger time	$\leq$ 30 ms
--------------	--------------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	thermoplastic

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

#### Use cases

Application	Security and safety systems
-------------	-----------------------------

#### Use

Differentiation characteristic 2 - Sales	enhanced contact protection
--	-----------------------------

#### Standards

Tested	conform VDE 0664 (EN 61008)
--------	-----------------------------

#### Safety

IK protection code against mechanical impacts	02
---	----

Protection index IP	IP20
---------------------	------

Protection	Enhanced contact protection
------------	-----------------------------

With enhanced contact protection	Yes
----------------------------------	-----

#### Identification

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
--------------------------	------------------------------------