



41527103

SCHUKO socket outlet with overvoltage protection and labelling field, K.5, alu

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Message	with acoustic fault signal
---------	----------------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Voltage

Overvoltage protection	according to EN 61643 and VDE 0675-6-11
------------------------	---

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	Plastic/metal
Surface appearance	matt

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
----------------------	--------------------------

Connection terminals	according to VDE 0620-1
Type of connection	with screw terminals
Equipment	
Lighting	with indicator LED for On/Error
Use cases	
Application	Security and safety systems
Use	
Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	Screw terminals
Safety	
IK protection code against mechanical impacts	07
Protection index IP	IP20
Protection	without enhanced contact protection
With enhanced contact protection	No
Identification	
Main design line	Berker K.5
Instructions	
Information text	Labelling field height arranged for P-touch strips 6 mm.