



41666089

**Soc.out. earth. contact USA/CAN NEMA 5-15 R, screw term., Q.x, p.white velv.**

#### Technical properties

##### Architecture

|                 |                |
|-----------------|----------------|
| Fixing mode     | flush-mounting |
| Number of poles | 2pole + earth  |

##### Configuration

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 125 V    |
| Rated voltage   | 125 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 15 A     |

##### Dimensions

|                 |       |
|-----------------|-------|
| Insertion depth | 19 mm |
|-----------------|-------|

##### Cover, door

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

##### Materials

|                       |                       |
|-----------------------|-----------------------|
| Colour of design line | polar white           |
| Colour                | polarwhite            |
| Colour                | white                 |
| RAL colour            | RAL 9010 - Pure white |
| Material              | thermoplastic         |
| Surface appearance    | velvety               |

##### Installation, mounting

|                   |   |
|-------------------|---|
| Installation mode | without spreader claws, for screw fastening |
|-------------------|---|

##### Connection

|                    |                      |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

##### Use

|  |                      |
|--|----------------------|
| Differentiation characteristic 3 - Sales | with screw terminals |
|--|----------------------|

##### Standards

|          |             |
|----------|-------------|
| Standard | NEMA 5-15 R |
|----------|-------------|

##### Safety

|   |    |
|---|----|
| IK protection code against mechanical impacts | 05 |
|---|----|

Protection

without enhanced contact protection

**Identification**

---

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

**Instructions**

---

Information text

Not UL-certified.