



4588

Modular FCC soc. out. 8/8pole shielded, cat.6 iso, com-tech

Technical properties

Architecture

Design to according to DIN EN 60603-7-51

Configuration

Category / ports cat.6A iso, Class EA, shielded

Connectivity

Outlet with straight outlet

Plug type only suitable for RJ45 plugs

Main electrical features

Rated voltage 72 V DC

Rated current 0.5 A

Voltage

Voltage suitable for PoE+

Dimensions

Insertion depth 35 mm

Frequency

Transmission bandwidth max. 500 MHz

Resistance

Shield contact resistance 100 mΩ

Signal contact resistance < 20 mΩ

Materials

Colour code A and B according to TIA/EIA-568-B.2

Material / surface Housing made of die-cast zinc

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Cat.6A iso/class EA according to DIN EN 50173-1:2011-09

Type of connection with IDC terminals

Contact with screen contacting 360° and strain relief

Equipment

Supporting plate / Supporting ring external eyelets on the supporting ring can be broken off for round designs

Safety

Cat.6 _{iso} , Class E _A , shielded	according to ISO/IEC 11801 A2
Protective screen	according to DIN EN 55022, Class B
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	with optional dust protection hinged covers

Use conditions

Operating temperature	-40...70 °C
-----------------------	-------------

Identification

Application, usage	Communication technology
Main design line	Communication technology