



47232089

SCHUKO soc. out., enhncd contact prot., R.1/R.3, p. white glossy

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Settings

Shading parameter	R1_biały
Laser parameter	R1_weiß

Equipment

Type of configuration	Laserdruck
-----------------------	------------

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8