



51018989

push-button complete for stairway light, screw terminals, S.1, p. white glossy

Technical properties

Architecture

Type of control unit single push button

Configuration

Switch mode Normally open contact

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 2 A

Dimensions

Depth 47.5 mm

Insertion depth 28.2 mm

Height 81 mm

Width 81 mm

Materials

Colour of design line polar white

Colour polarwhite

Colour white

RAL colour RAL 9010 - Pure white

Material duroplastic

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with screw terminals

Scope of delivery

Component with insert, frame, centre plate and red button

Equipment

Lighting without neon lamp

Use cases

Application

Light control

Use

Differentiation characteristic 3 - Sales

with screw terminals

Safety

Protection index IP

IP20

Identification

Main design line

Berker S.1