



6765096086

**Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,Q.x,ant.velv**

### Technical properties

#### Architecture

Number of poles 2pole + earth

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

#### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

#### Safety

Protection Enhanced contact protection

With enhanced contact protection Yes

#### Identification

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9