



6765106089

Soc.out. earth.pin+LED orient.,enhncd contact prot.,screw-in lift ,Q1/3,wh velv

Technical properties

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	32 mm
-----------------	-------

Power

Power consumption	0.25 W/0.35 VA
-------------------	----------------

Cover, door

Cover	Central cover plate
-------	---------------------

Detection

Sensor	integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness
--------	---

Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	velvety

Lighting control

Switch-off brightness	≈ 4 lx
Switch-on brightness	≈ 2 lx
Light intensity (white)	0.2 cd

LED control

LED	long service life of the LED, white LED light
-----	---

Installation, mounting		
Installation mode	with spreader claws	
Connection		
Conductor cross-section (rigid)	2.5	
Connection terminals	according to IEC 60884-1	
Type of connection	with screw-in lift terminals	
Cable		
Wiring	through-wiring possible, therefore also ideal for retrofitting	
Equipment		
Lighting	additional benefit by combination of a socket outlet with an orientation light	
Use		
Differentiation characteristic 2 - Sales	enhanced contact protection	
Differentiation characteristic 3 - Sales	Screw-in lift terminals	
Safety		
IK protection code against mechanical impacts	05	
REACH conform	Yes	
RoHS conform	Yes	
Halogen free	No	
Protection	Enhanced contact protection	
With enhanced contact protection	Yes	
Identification		
Main design line	Berker Q.1/Q.3/Q.7/Q.9	
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9	
Instructions		
Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.	