



6765107003

Soc.out. earth.pin+LEDorient.,enhncd contact prot.,screw-in lift term.,K5,al.lac

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Dimensions

Insertion depth 32 mm

Power

Power consumption 0.25 W/0.35 VA

Cover, door

Cover Central cover plate

Detection

Sensor integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness

Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance matt

Lighting control

Switch-off brightness ≈ 4 lx

Switch-on brightness ≈ 2 lx

Light intensity (white) 0.2 cd

LED control

LED long service life of the LED ; white LED light

Installation, mounting

Installation mode with spreader claws

Connection

Conductor cross-section (rigid)	max. 2.5 mm ²
Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals
Cable	
Wiring	through-wiring possible, therefore also ideal for retrofitting
Equipment	
Lighting	additional benefit by combination of a socket outlet with an orientation light
Use	
Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals
Safety	
IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
Identification	
Main design line	Berker K.5
Instructions	
Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.