



5036

## Push-button change-over contact illuminated

### Technical properties

#### Architecture

|                      |        |
|----------------------|--------|
| Type of control unit | rocker |
|----------------------|--------|

#### Functions

|                 |       |
|-----------------|-------|
| Switching angle | 3.5 ° |
|-----------------|-------|

#### Configuration

|             |   |
|-------------|---|
| Switch mode | change-over contact, usable as NC or NO |
|-------------|---|

#### Compatibility

|                         |    |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

#### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |

#### Electric current

|                           |      |
|---------------------------|------|
| Momentary-contact current | 10 A |
|---------------------------|------|

#### Dimensions

|                 |       |
|-----------------|-------|
| Depth           | 42 mm |
| Insertion depth | 31 mm |
| Height          | 71 mm |
| Width           | 71 mm |

#### Materials

|          |               |
|----------|---------------|
| Material | Plastic/metal |
|----------|---------------|

#### Installation, mounting

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

#### Connection

|                                 |                        |
|---------------------------------|------------------------|
| Conductor cross-section (rigid) | 2.5                    |
| Type of connection              | with plug-in terminals |

#### Equipment

|                         |                                     |
|-------------------------|-------------------------------------|
| Quantity of NC contacts | 1                                   |
| Quantity of NO contacts | 1                                   |
| Lighting                | for lighting and monitoring circuit |

#### Use cases

|             |   |
|-------------|---|
| Application | Barrier-free application, HVAC-control, Light control |
|-------------|---|

|                       |  |
|-----------------------|--|
| <b>Safety</b>         |  |
| Protection index IP   | IP20   |
| REACH conform         | Yes  |
| RoHS conform          | Yes  |
| Halogen free          | Yes  |
| <b>Identification</b> |  |
| Main design line      | Light control  |
| <b>Instructions</b>   |  |
| Information text      | spreader claws, insulated to the supporting ring, self-resetting |