



6765766012

**Soc.out. earth. pin, enhncd contact prot., screw-in lift term.,Q.1/Q.3,red velv.**

### Technical properties

#### Architecture

Number of poles 2pole + earth

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Mirror depth 14.5 mm

#### Cover, door

Cover Central cover plate

#### Materials

Design lines special colours red

Surface appearance velvety

Metallic colour No

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

#### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales with screw-in lift terminals

#### Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes
<b>Identification</b>	
Secondary design line(s)	Berker Q.3 ; Berker Q.1 ; Berker Q.7 ; Berker Q.9