



51018989

push-button complete for stairway light, screw terminals, S.1, p. white glossy

#### Technical properties

##### Architecture

Type of control unit single push button

##### Configuration

Switch mode Normally open contact

Antibacterial treatment No

##### Compatibility

IFTTT support available No

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

##### Electric current

Momentary-contact current 2 A

##### Dimensions

Depth 47.5 mm

Insertion depth 28.2 mm

Height 81 mm

Width 81 mm

##### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

##### Installation, mounting

Installation mode with spreader claws

##### Connection

Type of connection with screw terminals

##### Scope of delivery

Component with insert, frame, centre plate and red button

##### Equipment

Lighting without neon lamp

##### Use cases

Application

Light control

---

**Use**

Differentiation characteristic 3 - Sales

with screw terminals

---

**Safety**

REACH conform

Yes

RoHS conform

Yes

---

**Identification**

Main design line

Berker S.1