



6765766014

Soc.out. earth. pin,enhncd contact prot.,screw-in lift term.,Q.1/3,orange velv.

Technical properties

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	32 mm
Mirror depth	14.5 mm

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Design lines special colours	orange
Colour	orange
Colour	orange
RAL colour	RAL 2003 - Pastel orange
Material	duroplastic
Surface appearance	velvety

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw-in lift terminals

Safety

IK protection code against mechanical impacts	02
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Secondary design line(s)	Berker Q.3, Berker Q.1, Berker Q.7, Berker Q.9
--------------------------	--