



75164093



IP20

## B.IQ push-button 4gang, KNX - B.IQ, stainless steel, metal brushed

### Technical properties

#### Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Number of buttons	4

#### Dimensions

Assembling height	16.7 mm
Height	118.1 mm
Width	88.5 mm

#### Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

#### Screen

With display	No
--------------	----

#### Materials

Colour of design line	Stainless steel
Material / workmanship	metal brushed
Surface appearance	matt
Material family	Metal

#### LED control

LED	with blue operation LED and 8 white status LEDs
-----	---

#### Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

#### Scope of delivery

Bus connection included	No
-------------------------	----

#### Accessories included

Box	for installation in single standard wall boxes
-----	--

for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for stainless steel frames in the same "style" for additional applications, see the Design line B.7

Matching products

### Equipment

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

### Safety

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

### Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ