



75643130



**KNX glass sensor 3g thermostat, display, intg bus coupl. ,KNX-TS sensor, p.wh.**

### Technical properties

#### Functions

With room temperature controller Yes

Function with valve protection function ; for switch, push-button, dimmer, blind and thermostat functions

Operating mode controller operating modes: comfort, standby, night and frost/heat protection mode

#### Controls and indicators

With LED indication Yes

Operation operation by gently touching the sensor surfaces on the white LED

Indication / display LED display with symbol display ; display of operating mode, controller lockout, room/outside temperature, time (clock required)

Button / push-button with 2 additional display sensor surfaces

#### Connectivity

Encoding with button blocking function

#### Voltage

Voltage operation with non-choked output of KNX voltage supply possible (pay attention to current consumption) ; separate auxiliary power supply needed

#### Dimensions

Depth 37.7 mm

Depth 5.7 mm

Dimensions (W x H x D) 86 x 160 x 5.7 mm

Height 160 mm

Width 86 mm

#### Power

Current consumption 23 mA

#### Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

#### Screen

With display Yes

#### Materials

Colour of labelling 105,105,105

Colour of design line glass polar white

RAL colour	RAL 9010 - Pure white
Material family	Glass
<b>LED control</b>	
LED	with blue operation LED and 6 white status LEDs
<b>Installation, mounting</b>	
Installation mode	for vertical mounting
<b>Connection</b>	
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Parameterisation	single and two push-button operation parameterisable ; end customer display scope parameterisable
<b>Scope of delivery</b>	
Bus connection included	Yes
<b>Accessories included</b>	
Adapters	with adapter ring for dismantling protection and shadow gap formation
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x
<b>Equipment</b>	
With anti-theft/dismantling protection	Yes
Type of configuration	Laserdruck
Heating	for heating and/or cooling mode with/without auxiliary step
Control	for individual single room temperature control ; control parameter for heating / cooling unit pre-set ; for continuous (PI) or switched (2-point) control
<b>Use</b>	
Differentiation characteristic 2 - Sales	Display
Differentiation characteristic 3 - Sales	integrated bus coupling unit
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Temperature	additional connection for external temperature sensor ; temperature measurement via internal temperature sensor or external communication object
Energy efficiency class	IV (2%)
<b>Identification</b>	

Application, usage	KNX - operating systems
Main design line	KNX - Berker TS Sensor - configured
Secondary design line(s)	Berker TS Sensor ; KNX
<b>Instructions</b>	
Information text	Only suitable for KNX.