



6765096089

**Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,Q.x,wh velv**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Dimensions

Insertion depth	32 mm
-----------------	-------

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	duroplastic
Surface appearance	velvety

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

##### Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

##### Safety

Protection	Enhanced contact protection
With enhanced contact protection	Yes

**Identification**

---

Main design line

Berker Q.1/Q.3/Q.7/Q.9

---

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9