



75665592



B.IQ push-button 5gang thermostat, display, KNX - B.IQ, glass black

Technical properties

Functions

With room temperature controller	Yes
Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	5
Operation	one push-button operation for switching, pushing, shutters and dimming

Dimensions

Assembling height	16.7 mm
Width of rail mounted device (RMD)	0 modules
Height	178.8 mm
Width	88.5 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	Yes
--------------	-----

Materials

Colour of design line	glass black
RAL colour	RAL 9005 - Jet black
Material	glass
Material family	Glass

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
-----	--

for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for glass frames in the same "style" for additional applications, see the Design line B.7

Matching products

Equipment

Product type: product type: B.IQ

Control for individual single room temperature control

Software

Update with flash-controller technology

Safety

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Energy efficiency class IV (2%)

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Release issue 2.6

Main design line KNX - Berker B.IQ

Secondary design line(s) Berker B.IQ, KNX