



75665593



**B.IQ push-b. 5gang thermostat, display, KNX - B.IQ, stainl. steel metal brushed**

**Technical properties**

**Functions**

With room temperature controller	Yes
Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

**Compatibility**

Extension unit	extension unit for light scene push-button
----------------	--

**Controls and indicators**

With LED indication	Yes
Number of buttons	5
Operation	one push-button operation for switching, pushing, shutters and dimming

**Dimensions**

Assembling height	16.7 mm
Width of rail mounted device (RMD)	0 modules
Height	178.8 mm
Width	88.5 mm

**Measurement**

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

**Screen**

With display	Yes
--------------	-----

**Materials**

Colour of design line	Stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	metal brushed
Material	stainless steel
Material family	Metal

**Settings**

Parameterisation	single and two push-button operation parameterisable
------------------	--

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Accessories included**

Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for stainless steel frames in the same "style" for additional applications, see the Design line B.7
<b>Equipment</b>	
Product type:	product type: B.IQ
Control	for individual single room temperature control
<b>Software</b>	
Update	with flash-controller technology
<b>Safety</b>	
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)
<b>Identification</b>	
Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ, KNX