



75665691

Technical properties

Functions

Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

Number of buttons	5
Operation	one push-button operation for switching, pushing, shutters and dimming

Dimensions

Depth	87.8 mm
Width of rail mounted device (RMD)	0 modules
Height	187.8 mm
Width	88.5 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Materials

Colour of design line	glass polar white
RAL colour	RAL 9010 - Pure white
Material	glass

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Accessories included

Box	for installation in single standard wall boxes
Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Equipment

Product type:	product type: B.IQ
Control	for individual single room temperature control

Software

Update

with flash-controller technology

Safety

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Energy efficiency class

IV (2%)

Identification

Application, usage

KNX - operating systems

Product family

product family: push-button

Release issue

2.6

Main design line

KNX - Berker B.IQ

Secondary design line(s)

Berker B.IQ, KNX

Instructions

Information text

IR hand-held transmitter, order no. 2779