



6765836086

Soc.out. earth.pin+hinged cover,enhncd contact prot.,screw-in lift ,Q.x,ant.

Technical properties

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Dimensions

Insertion depth	31.3 mm
-----------------	---------

Cover, door

Hinged covers	with hinged cover that falls back
Cover	Central cover plate

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety
Metallic colour	No

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw-in lift terminals

Safety

IK protection code against mechanical impacts		05
REACH conform		Yes
RoHS conform		Yes
Halogen free		No
Protection	Enhanced contact protection	
With enhanced contact protection		Yes

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9	
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9	