



75163599



IP20

## B.IQ push-button 3gang comf, KNX - B.IQ, p. white, matt, plastic

### Technical properties

#### Functions

|                                  |    |
|----------------------------------|----|
| With room temperature controller | No |
|----------------------------------|----|

|          |   |
|----------|---|
| Function | for switch, push-button, dimmer and shutter functions |
|----------|---|

#### Compatibility

|                |  |
|----------------|--|
| Extension unit | extension unit for light scene push-button |
|----------------|--|

#### Controls and indicators

|                     |     |
|---------------------|-----|
| With LED indication | Yes |
|---------------------|-----|

|                   |   |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

|           |   |
|-----------|---|
| Operation | activation of second user level via object ; one push-button operation for switching, pushing, shutters and dimming |
|-----------|---|

#### Dimensions

|        |         |
|--------|---------|
| Height | 88.5 mm |
|--------|---------|

|       |         |
|-------|---------|
| Width | 88.5 mm |
|-------|---------|

#### Measurement

|                   |   |
|-------------------|---|
| Value transmitter | value transmitter for dimming, position, brightness and temperature values 1 and 2 byte |
|-------------------|---|

#### Screen

|              |    |
|--------------|----|
| With display | No |
|--------------|----|

#### Materials

|                     |             |
|---------------------|-------------|
| Colour of labelling | 105,105,105 |
|---------------------|-------------|

|                       |             |
|-----------------------|-------------|
| Colour of design line | polar white |
|-----------------------|-------------|

|            |                       |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

|                    |      |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

|                           |           |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

#### LED control

|     |  |
|-----|--|
| LED | with blue operation LED and 6 white status LEDs (labelling field illumination) |
|-----|--|

#### Connection

|                   |                                     |
|-------------------|-------------------------------------|
| Bus coupling unit | for bus coupling unit flush-mounted |
|-------------------|-------------------------------------|

#### Settings

|                               |            |
|-------------------------------|------------|
| Supported configuration modes | system, PB |
|-------------------------------|------------|

|                  |  |
|------------------|--|
| Parameterisation | single and two push-button operation parameterisable |
|------------------|--|

**Scope of delivery**

|                         |    |
|-------------------------|----|
| Bus connection included | No |
|-------------------------|----|

**Accessories included**

|     |  |
|-----|--|
| Box | for installation in single standard wall boxes |
|-----|--|

|                   |  |
|-------------------|--|
| Matching products | for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for plastic frames in the same "style" for additional applications, see the Design line B.7 |
|-------------------|--|

**Equipment**

|                            |   |
|----------------------------|---|
| Number of actuation points | 6 |
|----------------------------|---|

|  |     |
|--|-----|
| With anti-theft/dismantling protection | Yes |
|--|-----|

|                       |            |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

|               |                    |
|---------------|--------------------|
| Product type: | product type: B.IQ |
|---------------|--------------------|

**Safety**

|               |     |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

|            |                             |
|------------|-----------------------------|
| Protection | with dismantling protection |
|------------|-----------------------------|

|       |   |
|-------|---|
| Alarm | alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte |
|-------|---|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

**Identification**

|                    |                         |
|--------------------|-------------------------|
| Application, usage | KNX - operating systems |
|--------------------|-------------------------|

|                |                             |
|----------------|-----------------------------|
| Product family | product family: push-button |
|----------------|-----------------------------|

|                  |                   |
|------------------|-------------------|
| Main design line | KNX - Berker B.IQ |
|------------------|-------------------|

|                          |                   |
|--------------------------|-------------------|
| Secondary design line(s) | KNX ; Berker B.IQ |
|--------------------------|-------------------|