



75164094

IP20

B.IQ push-button 4gang, KNX - B.IQ, al., al. anodised

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	4
-------------------	---

Dimensions

Assembling height	16.7 mm
-------------------	---------

Height	118.1 mm
--------	----------

Width	88.5 mm
-------	---------

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	Aluminium
-----------------------	-----------

Colour	aluminium
--------	-----------

RAL colour	RAL 9006 - White aluminium
------------	----------------------------

Material / workmanship	aluminium, anodised
------------------------	---------------------

Material	Aluminium
----------	-----------

Surface appearance	matt
--------------------	------

Type of surface treatment	Anodised
---------------------------	----------

Material family	Metal
-----------------	-------

LED control

LED	with blue operation LED and 8 white status LEDs
-----	---

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Scope of delivery	
Bus connection included	No
Accessories included	
Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for aluminium frames in the same "style" for additional applications, see the Design line B.7
Equipment	
Number of actuation points	8
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ