


80262270



## K.x/Q.x KNX (TP+EASY) Movement detector module 2,20m

### Technical properties

#### Functions

Max. temporisation 30 mn

push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover ; Motion detector functions: switching, dimming, roller shutter/blind, timer ; additional channel for independent of brightness detector mode

Easy link functions

Function Presence simulation ; with party function

integrated button for manual control of bus functions can be configured ; Push-button functions for switching, dimming, blind, value transmitter, scene, priority ; Specification of the controller operating mode ; integrated temperature sensor with output of the measured values via object ; parameter defineable lock function

Function

Slide switch with slide switch for OFF/automatic/ON

Operating mode with 3 operating modes: automatic/permanent ON/permanent OFF

#### Configuration

Channels two function channels for brightness-dependent functions ; additional channel for independent of brightness detector mode

#### Controls and indicators

Push-buttons with button for automatic/permanent ON/permanent OFF

#### Voltage

Operating voltage over bus 21...32 V DC

#### Electric current

Bus current consumption (data transfer) 10 mA

#### Dimensions

Optimum mounting height 2.2 m

#### Measurement

Detection field, rectangular shaped  $\approx 8 \times 12$  m

#### Reach distance

Max. transmission range frontally 8 m

Max. transmission range sideways 6 m

#### Detection

Detection angle vertical 0 / 7 °

Detection angle, settable	each side $\approx 45 \dots 90^\circ$
Detection angle horizontal	90 / 180 °
Sensor type	detector of movement
<b>Materials</b>	
Surface appearance	other
<b>Lighting control</b>	
Response brightness, adjustable	$\approx 5 \dots 1000 \text{ lx}$ , daytime operation
<b>LED control</b>	
LED	Operating mode display via status LED, red/green/orange
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	0 W
<b>Installation, mounting</b>	
Installation mode	with spreader claws ; with dismantling protection
<b>Connection</b>	
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
<b>Settings</b>	
Supported configuration modes	system, easy
Min. temporisation	10 s
Delay time, adjustable	10 s...30 mn
<b>Use</b>	
Differentiation characteristic 2 - Sales	with integrated temperature sensor
Differentiation characteristic 3 - Sales	with integral bus coupling unit
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Application, usage	KNX - sensors
Main design line	KNX - Berker Q.x/K.x
Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9 ; Berker K.1 ; Berker K.5
<b>Instructions</b>	
Information text	Continuous direct sunlight penetrating the upward-pointing detection plane can result in failure of the motion detector. Only suitable for indoor areas!