




80660100

IP21 IK04



KNX room cont., colourdisplay, intg bus coupling unit, KNX

Technical properties

Functions

switching of scenes (1..8) possible ; operating mode heating, cooling or heating/cooling can be selected ; switching PI-control (PWM) or switching 2-point control can be selected ; heating type warm water heating, warm water underfloor heating, electric heating, electric underfloor heating or split unit can be selected ; cooling type cooling ceiling, convector fan or split unit can be selected ; comfort, standby, night-time reduction, frost/heat protection operating mode switchable via scene ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

with keylock ; with holiday switching ; with frost protection function ; for switch, dimmer and shutter functions ; deactivate automatic function

Function

operating modes heating, cooling, heating/cooling or background heating and additional heating/cooling can be selected ; control modes switching PI-control (PWM), continuous PI control or switching 2-point control can be selected ; heating types warm water heating, warm water underfloor heating, electric heating, electric underfloor heating, split unit or adjustable via object ; Push-button functions for switching, dimming, roller shutter/blind, value transmitter 1 and 2 byte, thermostat, scene, priority

Function

Controls and indicators

Operation

Operation via sensitive Touch control surface

Indication / display

display of set or actual temperature ; Screen saver ; LC display with symbol display ; Time and date display ; to display and initiate actions

Voltage

Auxiliary voltage

24 V DC

Operating voltage over bus

21...32 V DC

Electric current

Current consumption (operation)

25 mA

Bus current consumption (data transfer)

max. 10 mA

Dimensions

Insertion depth

32 mm

Dimensions of display (W x H)

38.28 x 30.26 mm

Width of rail mounted device (RMD)

0 modules

Width

71 mm

Screen

TFT screen size

1.93 "

Installation, mounting

Subject to technical modifications

Installation mode	with spreader claws ; for flush-mounted and hollow-wall mounting ; for single mounting ; for vertical mounting
Connection	
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Connection	with additional connection for external floor temperature sensor/remote sensor
Settings	
Supported configuration modes	system, easy
Time	with automatic summer/winter time change-over
Equipment	
Heating	for heating and/or cooling mode ; heating or cooling possible in 2 stages
Control	for individual single room temperature control ; control parameter for heating / cooling unit pre-set
Use	
Differentiation characteristic 2 - Sales	with colour display
Differentiation characteristic 3 - Sales	integrated bus coupling unit
Safety	
REACH conform	No
Halogen free	No
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
Temperature	comfort, standard and night temperature ; temperature measurement via internal and/or connectable temperature sensor with average determination ; additional connection for external temperature sensor
Energy efficiency class	IV (2%)
Identification	
Application, usage	KNX - operating systems
Product family	Product family: heating, ventilation, air conditioning
Composition	basis element
Main design line	KNX
Instructions	
Information text	The KNX room controller in comparison with the thermostat also has push-button functions and can thus control all subsystems in a room.