



75663590



B.IQ push-button 3gang thermostat, display, KNX - B.IQ, glass p. white

Technical properties

Functions

With room temperature controller Yes

Function with valve protection function

Timers with room temperature timer and 2-week timer functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Width of rail mounted device (RMD) 0 modules

Height 119.6 mm

Width 88.5 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Materials

Colour of design line glass polar white

RAL colour RAL 9010 - Pure white

Material glass

Material family Glass

LED control

LED with blue operation LED and 6 white status LEDs (labelling field illumination)

Settings

Parameterisation single and two push-button operation parameterisable

Accessories included

Box for installation in single standard wall boxes

Matching products for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for glass frames in the same "style" for additional applications, see the Design line B.7

Equipment

Product type:	product type: B.IQ
Control	for individual single room temperature control

Software

Update	with flash-controller technology
--------	----------------------------------

Safety

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ
