


85145173



IP20

## KNX radio button 1gang quicklink, K.5, stainless steel matt, lacq.

### Technical properties

#### Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

#### Connectivity

Radio protocol	KNX Radio
Receiver category	2

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Materials

Colour of design line	stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

#### Equipment

Number of radio channels	2
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

#### Safety

Protection	with dismantling protection
------------	-----------------------------

#### Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

#### Identification

Application, usage	Light control, KNX radio- operating systems
Main design line	Berker K.5
Secondary design line(s)	Berker K.5