



85648126



IP20

KNX radio button 4gang quicklink, Q.x, ant. velvety, lacq.

Technical properties

Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
--------------------------	--

Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory
---------------------	--

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Power

Radio transmission power	< 10 mW
--------------------------	---------

Materials

Colour of design line	anthracite
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

Equipment

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

Safety

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Light control, KNX radio- operating systems
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text	Extended operating options on 1gang inserts through 2 additional, freely-configurable radio channels.
------------------	---

