



85145182



IP20

quicklink

## KNX radio button 1gang quicklink, S.1, white glossy

### Technical properties

#### Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
--------------------------	--

Function	Configurable transmission and/or reception behaviour ; reset function (to factory setting) ; easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
----------	--

Light scenes	scene saving lockable
--------------	-----------------------

Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory
---------------------	--

#### Controls and indicators

Operation	operating areas configurable as one or two-area operation
-----------	---

Button / push-button	with configuration and function button
----------------------	--

#### Connectivity

Radio protocol	KNX Radio
----------------	-----------

Receiver category	2
-------------------	---

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Materials

Colour of design line	white
-----------------------	-------

Surface appearance	glossy
--------------------	--------

#### LED control

LED	with configuration and function LEDs ; LED application module/insert compatibility display
-----	--

#### Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

#### Settings

Programming	top and bottom operating area on 1-gang switching/dimming inserts and network insert are freely configurable ; toolless quicklink configuration using buttons and LED display
-------------	---

#### Equipment

Number of radio channels	2
--------------------------	---

Number of quicklink links	max. 20 transmitter/receiver
---------------------------	------------------------------

Transmitter duty cycle 1 %

Brightness switch-on brightness level for each operating area on configuration with dimmer insert, power failure proof, storable

---

**Safety**

REACH conform No

RoHS conform Yes

Halogen free No

Protection with dismantling protection

---

**Use conditions**

Operating temperature -5...45 °C

Energy-saving low intrinsic energy requirement

Relative humidity (without condensation) 0...65 % (without condensation)

---

**Identification**

Application, usage Light control ; KNX radio- operating systems

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Electronics platform ; Berker S.1 ; Berker B.3 ; Berker B.7