



85655273

Configurationsmodus
KNX-RF
quicklink



IP20

KNX radio wall-transmitter 1gang flat quicklink, K.5, stainl. steel matt, lacq.

Technical properties

Functions

ETS additional functions

ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value

Quicklink functions

quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol

KNX Radio

Receiver category

2

Dimensions

Assembling height

14 mm

Frequency

Radio transmission frequency

868.3 MHz

Power

Radio transmission power

< 10 mW

Battery

Battery service life [years]

≈ 5

Materials

Colour of design line

stainless steel

RAL colour

RAL 9022 - Pearl light grey

Material / workmanship

lacquered

Material

thermoplastic

Surface appearance

matt

Equipment

Number of radio channels

2

Number of quicklink links

max. 20 transmitter/receiver

Transmitter duty cycle

1 %

Safety

REACH conform

No

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Relative humidity (without condensation)

0...65 % (without condensation)

Identification	
Application, usage	KNX radio- operating systems
Main design line	Berker K.5
Secondary design line(s)	Berker K.5