



85655283

Configurationsmodus
KNX-RF
quicklink



IP20

KNX radio wall-transmitter 1gang flat quicklink, S.1/B.7, al., matt, lacq.

Technical properties

Functions

ETS additional functions

ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value

Quicklink functions

quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol

KNX Radio

Receiver category

2

Dimensions

Assembling height

14 mm

Frequency

Radio transmission frequency

868.3 MHz

Power

Radio transmission power

< 10 mW

Battery

Battery service life [years]

≈ 5

Materials

RAL colour

RAL 9006 - White aluminium

Material / workmanship

lacquered

Material

thermoplastic

Surface appearance

matt

Equipment

Number of radio channels

2

Number of quicklink links

max. 20 transmitter/receiver

Transmitter duty cycle

1 %

Safety

REACH conform

No

Protection

with dismantling protection

Use conditions

Operating temperature

-5...45 °C

Relative humidity (without condensation)

0...65 % (without condensation)

Identification

Application, usage	KNX radio- operating systems
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7