



85745183



IP20



## KNX radio blind time switch quicklink, display, S.1/B.7, al., matt, lacq.

### Technical properties

#### Functions

Astronomic time shift	± 2 h
Running time	2 mn
Random number generator for holiday program	± 15 mn
ETS additional functions	ETS additional functions: +6 scenes, operating mode, status display, 2 x alarm
Function	reset function (to factory setting) ; with keylock ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection) ; Configurable transmission and/or reception behaviour ; easy additional functions: +6 scenes, 1 up/down operating mode
Light scenes	slat position storable for scene ; scene opening via KNX radio appliances
Quicklink functions	quicklink functions for integration into the individual, group and master control of blinds/shutters ; quicklink functions: blind, 2 scenes, forced control, up/down push-button
Slide switch	with switchover manual/automatic mode
Power reserve	≈ 8 h

#### Controls and indicators

Indication / display	indication of the application module/insert compatibility in the display ; LC display contrast is adjustable ; LC display illuminated during operation
----------------------	--

#### Connectivity

Radio protocol	KNX Radio
----------------	-----------

#### Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Measurement

Running accuracy	± 3 min/year
------------------	--------------

#### Battery

Power reserve [years]	0 h
-----------------------	-----

#### Detection

Sensor	sun protection and twilight-controlled lowering with radio brightness sensor
--------	--

#### Materials

Colour of design line	aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt
<b>Connection</b>	
Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
<b>Settings</b>	
Minimum slat adjustment time	≈ 150 ms
Lamella adjustment on signal duration	< 1 s
Lamella adjustment on button-press	< 0.5 s
Programs	astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable ; standalone programme, radio and extension unit commands are not executed ; holiday programme for random variation of the operation times in automatic operation
Time	with automatic summer-/winter time switching (can be switched off)
<b>Equipment</b>	
Number of operation times for up/down	20/day
Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Self-retaining for 2 min on signal length	> 1 s
Self-retaining for 2 min on button-press	> 0.5 s
Change-over time for change of direction	< 0.6 s
Cylinder	2 independent preset programme memories, individually adaptable
<b>Use</b>	
Differentiation characteristic 2 - Sales	with display
<b>Safety</b>	
Protection index IP	IP20
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
<b>Identification</b>	
Application, usage	Blind control ; KNX radio- operating systems
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Electronics platform ; Berker S.1 ; Berker B.3 ; Berker B.7
<b>Instructions</b>	
Special note text	Can be switched to orientation led by extension unit.