



85745226



IP20



KNX radio timer quicklink, display, Q.x, ant. velvety, lacq.

Technical properties

Functions

Astronomic time shift	± 2 h
Random number generator	± 15 mn

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display
--------------------------	--

Function	reset function (to factory setting) ; Configurable transmission and/or reception behaviour ; Party function, no execution of automatic, radio and extension unit commands (switch protection) ; with keylock ; easy additional functions: +6 scenes, dimming, 1 up/down button control, priority
----------	--

Quicklink functions	quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control
---------------------	--

Slide switch	with switchover manual/automatic mode
--------------	---------------------------------------

Power reserve	≈ 8 h
---------------	-------

Controls and indicators

Indication / display	LC display illuminated during operation ; indication of the application module/insert compatibility in the display ; LC display contrast is adjustable
----------------------	--

Connectivity

Radio protocol	KNX Radio
----------------	-----------

Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Running accuracy	± 3 min/year
------------------	--------------

Battery

Power reserve [years]	0 a
-----------------------	-----

Materials

Colour of design line	anthracite
-----------------------	------------

Material / workmanship	lacquered
------------------------	-----------

Surface appearance	velvety
--------------------	---------

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

Settings

Programs	astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable ; standalone programme, radio and extension unit commands are not executed ; holiday programme for random variation of the switching times in automatic operation
Time	with automatic summer-/winter time switching (can be switched off)

Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Number of switching times for on/off	20
Cylinder	2 independent preset programme memories, individually adaptable

Use

Differentiation characteristic 2 - Sales	with display
--	--------------

Safety

REACH conform	No
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Light control ; KNX radio- operating systems
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9