




85745239



IP20



## KNX radio timer quicklink, display, R.1/R.3/1930/R.cl., p. white glossy

### Technical properties

#### Functions

Astronomic time shift	± 2 h
Random number generator	± 15 mn

#### ETS additional functions

ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display

#### Function

reset function (to factory setting) ; Configurable transmission and/or reception behaviour ; Party function, no execution of automatic, radio and extension unit commands (switch protection) ; with keylock ; easy additional functions: +6 scenes, dimming, 1 up/down button control, priority

#### Quicklink functions

quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control

#### Slide switch

with switchover manual/automatic mode

#### Power reserve

≈ 8 h

### Controls and indicators

#### Indication / display

LC display illuminated during operation ; indication of the application module/insert compatibility in the display ; LC display contrast is adjustable

### Connectivity

#### Radio protocol

KNX Radio

### Dimensions

#### Width of rail mounted device (RMD)

0 modules

#### Diameter

58 mm

### Power

#### Radio transmission power

< 10 mW

### Measurement

#### Running accuracy

± 3 min/year

### Battery

#### Power reserve [years]

0 a

### Materials

#### Colour of design line

polar white

#### Surface appearance

glossy

### Connection

#### Bus connection

integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

**Settings**

Programs	astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable ; standalone programme, radio and extension unit commands are not executed ; holiday programme for random variation of the switching times in automatic operation
Time	with automatic summer-/winter time switching (can be switched off)

**Equipment**

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Number of switching times for on/off	20
Cylinder	2 independent preset programme memories, individually adaptable

**Use**

Differentiation characteristic 2 - Sales	with display
--	--------------

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

**Identification**

Application, usage	Light control ; KNX radio- operating systems
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
Secondary design line(s)	Electronics platform ; Berker R.1 ; Berker R.3 ; Serie 1930 ; Series R.classic

**Instructions**

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--