



85346183



IP20

KNX radio motion det. comf 2.2 m quicklink, S.1/B.7, al., matt, lacq.

Technical properties

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value, brightness display, movement scene loading, no movement scene loading
--------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Function	with keylock
----------	--------------

Quicklink functions	quicklink functions: switching, dimming, 2 scenes, time switching, NO contact push-button, Memory, forced control, Master-Slave
---------------------	---------------------------------------------------------------------------------------------------------------------------------

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Assembling height	34 mm
Nominal mounting height	2.2 m

Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Detection field, rectangular shaped	≈ 8 x 12 m
-------------------------------------	------------

Reach distance

Range, frontal	≈ 8 m
Range, frontal (at 1.1 m installation height)	≈ 4 m
Range, side	each ≈ 6 m
Range, side (at 1.1 m installation height)	each ≈ 3 m

Detection

Number of detection levels	2
Detection angle, settable	each side ≈ 45...90 °

Materials

RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

Lighting control

Response brightness, adjustable ≈ 5...1000 lx , daytime operation

Settings

Response sensitivity, settable 10...100 %

Delay time, adjustable ≈ 1 s...3 h

Switch-off pre-warning to dimming value
50% for 30 s

Equipment

Number of radio channels 1

Number of quicklink links max. 20 transmitter/receiver

Transmitter duty cycle 1 %

Safety

Protection with dismantling protection

Use conditions

Operating temperature -5...45 °C

Relative humidity (without condensation) 0...65 % (without condensation)

Identification

Application, usage Motion detector

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1, Berker B.3, Berker B.7
