



85745288



**KNX radio timer quicklink, display, S.1/B.3/B.7, p. white, matt, plastic**

**Technical properties**

**Functions**

|                         |         |
|-------------------------|---------|
| Astronomic time shift   | ± 2 h   |
| Random number generator | ± 15 mn |

ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display

ETS additional functions

reset function (to factory setting) ; Configurable transmission and/or reception behaviour ; Party function, no execution of automatic, radio and extension unit commands (switch protection) ; with keylock ; easy additional functions: +6 scenes, dimming, 1 up/down button control, priority

Function

quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control

Quicklink functions

Slide switch with switchover manual/automatic mode

Slide switch

Power reserve ≈ 8 h

Power reserve

**Controls and indicators**

LC display illuminated during operation ; indication of the application module/insert compatibility in the display ; LC display contrast is adjustable

Indication / display

**Connectivity**

Radio protocol KNX Radio

Radio protocol

**Dimensions**

Width of rail mounted device (RMD) 0 modules

Width of rail mounted device (RMD)

**Power**

Radio transmission power < 10 mW

Radio transmission power

**Measurement**

Running accuracy ± 3 min/year

Running accuracy

**Battery**

Power reserve [years] 0 a

Power reserve [years]

**Materials**

Colour of design line polar white

Colour of design line

Surface appearance matt

Surface appearance

**Connection**

Bus connection integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system

Bus connection

**Settings**

|  |  |
|--|--|
| Programs                                 | astro programme for sunrise/sundown switching with city/country or co-ordinate input, individually adaptable ; standalone programme, radio and extension unit commands are not executed ; holiday programme for random variation of the switching times in automatic operation |
| Time                                     | with automatic summer-/winter time switching (can be switched off)   |
| <b>Equipment</b>                         |  |
| Number of radio channels                 | 1  |
| Number of quicklink links                | max. 20 transmitter/receiver   |
| Number of switching times for on/off     | 20   |
| Cylinder                                 | 2 independent preset programme memories, individually adaptable  |
| <b>Use</b>                               |  |
| Differentiation characteristic 2 - Sales | with display   |
| <b>Safety</b>                            |  |
| REACH conform                            | No   |
| RoHS conform                             | Yes  |
| Halogen free                             | No   |
| Protection                               | with dismantling protection  |
| <b>Use conditions</b>                    |  |
| Operating temperature                    | -5...45 °C   |
| Energy-saving                            | low intrinsic energy requirement   |
| Relative humidity (without condensation) | 0...65 % (without condensation)  |
| <b>Identification</b>                    |  |
| Application, usage                       | Light control ; KNX radio- operating systems   |
| Main design line                         | Berker S.1/B.3/B.7   |
| Secondary design line(s)                 | Electronics platform ; Berker S.1 ; Berker B.3 ; Berker B.7  |