



85346188



IP20

KNX radio motion det. comf 2.2 m quicklink, S.1/B.3/B.7, p. white, matt, plastic

Technical properties

Functions

Mode of operation	μ-processor controlled mode of operation
ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value, brightness display, movement scene loading, no movement scene loading
Function	reset function (to factory setting) ; Party function for switching on for 2 hours ; with memory function for presence simulation ; with keylock ; Switch-off pre-warning on dimmer inserts ; Teach function for response brightness via button
Light scenes	scene opening via KNX radio appliances ; scene saving lockable
Quicklink functions	quicklink functions: switching, dimming, 2 scenes, time switching, NO contact push-button, Memory, forced control, Master-Slave

Compatibility

Extension unit	optional operation of extension units using installation push-button
----------------	--

Controls and indicators

Operation	remote control via quicklink transmitter
Button / push-button	with configuration and function button ; with button for on/off/automatic/memory/party function

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Assembling height	34 mm
Nominal mounting height	2.2 m

Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Measurement

Detection field, rectangular shaped	≈ 8 x 12 m
-------------------------------------	------------

Reach distance

Range, frontal	≈ 8 m
Range, frontal (at 1.1 m installation height)	≈ 4 m

Range, side	each ≈ 6 m
Range, side (at 1.1 m installation height)	each ≈ 3 m

Detection

Number of detection levels	2
Detection angle, settable	each side ≈ 45...90 °

Materials

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt

Lighting control

Response brightness, adjustable	≈ 5...1000 lx , daytime operation
---------------------------------	-----------------------------------

LED control

LED	LED application module/insert compatibility display ; with configuration and function LEDs ; with operation and status LED, red/green/orange
-----	--

Connection

Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
----------------	--

Settings

Response sensitivity, settable	10...100 %
Delay time, adjustable	≈ 1 s...3 h
Switch-off pre-warning to dimming value 50% for	30 s

Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Motion detector ; KNX radio- sensors
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Electronics platform ; Berker S.1 ; Berker B.3 ; Berker B.7