



AD184

## RCBO 1M 1P 10kA C-6A 30mA AC

### Technical properties

#### Architecture

Neutral position	right
Number of protected poles	1
Number of poles	1 P
Curve	C

#### Functions

Concurrently switching N-neutral	No
----------------------------------	----

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	10 kA
Rated operational voltage $U_e$	230 / 240 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	250 V
Max operating voltage	253 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	30 mA
Rated current	6 A
Breaking and opening capacity	6 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 $I_n$
Magnetic regulating current	5 / 10 $I_n$
Rated short circuit breaking capacity $I_{cn}$ under 230V AC according IEC60898-1	10 kA

#### Electric current / temperature

Rating current -25°C	7.72 A
Rating current -20°C	7.58 A
Rating current -15°C	7.43 A
Rating current -10°C	7.29 A
Rating current -5°C	7.14 A
Rating current 0°C	6.99 A
Rating current 5°C	6.83 A

Rating current 10°C	6.67 A
Rating current 15°C	6.51 A
Rating current 20°C	6.35 A
Rating current 25°C	6.18 A
Rating current 30°C	6 A
Rating current 35°C	5.82 A
Rating current 40°C	5.63 A
Rating current 45°C	5.44 A
Rating current 50°C	5.24 A
Rating current 55°C	5.03 A
Rating current 60°C	4.81 A

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85

#### Dimensions

Depth of installed product	70 mm
Height of installed product	115 mm
Width of installed product	17.5 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	1.5 W
Power loss per pole at In	1.24 W

#### Tripping

Protected against nuisance tripping	No
-------------------------------------	----

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

#### Connection

Connection cross-section at output with screw, for flexible conductor	1 / 16 mm <sup>2</sup>
Connection cross-section at output with screw, for massive conductor	1 / 25 mm <sup>2</sup>
Connection cross-section for rigid conductor, upstream terminals with screws	1 / 25 mm <sup>2</sup>
Connection cross-section of the access with screws, with flexible conductor	1 / 16 mm <sup>2</sup>

#### Standards

Standard text	IEC 61009-1 ; EN 61009-1
---------------	--------------------------

<b>Safety</b>	
Protection index IP	IP20
Residual current type	AC
<b>Use conditions</b>	
Class of energy limitation I <sup>2</sup> t	3
Altitude	2000 m