



BA7A40080

Slotted panel trunking made of PVC BA7A 40x80mm grey

Technical properties

Architecture

| | |
|----------|----|
| Flexible | No |
|----------|----|

Configuration

| | |
|-------------------------|---------|
| Side wall configuration | Slotted |
|-------------------------|---------|

Electric current

| | |
|---------------------|-----|
| Current leak stable | Yes |
|---------------------|-----|

Dimensions

| | |
|-----------------|-------|
| Trunking height | 40 mm |
|-----------------|-------|

| | |
|--------|---------|
| Length | 2000 mm |
|--------|---------|

| | |
|----------------|-------|
| Trunking width | 80 mm |
|----------------|-------|

| | |
|------------|------|
| Slot width | 6 mm |
|------------|------|

| | |
|--------------|--------|
| Tongue width | 6.5 mm |
|--------------|--------|

Cover, door

| | |
|-----------|-------|
| Lid shape | loose |
|-----------|-------|

Materials

| | |
|----------------|---------|
| Material group | plastic |
|----------------|---------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

Installation, mounting

| | |
|---------------|-------------------|
| Base punching | EN 50085-2-3:1999 |
|---------------|-------------------|

| | |
|-------------|-----------------|
| Fixing type | bottom punching |
|-------------|-----------------|

Cable

| | |
|--|----|
| Number of wires 1,5 mm ² - 40% filling degree | 73 |
|--|----|

| | |
|-------------------------------|----------------------|
| Internal/useful cross section | 2118 mm ² |
|-------------------------------|----------------------|

| | |
|--|----|
| Number of wires 2,5 mm ² - 40% filling degree | 52 |
|--|----|

| | |
|--|-----|
| Number of wires 1,0 mm ² - 40% filling degree | 101 |
|--|-----|

Standards

| | |
|-----------|-------------|
| Approvals | EN50085-2-3 |
|-----------|-------------|

| | |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

| | |
|----------------------|----|
| UL 94 classification | V0 |
|----------------------|----|

Safety

| | |
|--------------------------|------------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | No |
| Fireproof classification | M1 |
| temperatur | |
| Ambient temperature | -5...60 °C |