



85656231



IP20

KNX radio wall-transmitter 2gang flat quicklink, R.1/R.3, black glossy

Technical properties

Functions

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Function	reset function (to factory setting), easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Controls and indicators

Operation	operating areas configurable as one or two-area operation
Button / push-button	with configuration button

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Dimensions

Assembling height	14 mm
-------------------	-------

Frequency

Radio transmission frequency	868.3 MHz
------------------------------	-----------

Power

Radio transmission power	< 10 mW
--------------------------	---------

Battery

Battery service life [years]	≈ 5
Battery / storage battery	with lithium coin cell battery 3 V type: CR 2430

Materials

Colour of labelling	217,217,217
Colour of design line	black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

LED control

LED	with configuration LED, with transmission status and battery status LED, red/green/orange
-----	---

Installation, mounting

Installation mode	for flat surface mounting and extension of combinations
Connection	
Bus connection	integration in the KNX radio/TP gateway, surface-mounted, into the KNX TP system
Settings	
Programming	toolless quicklink configuration using buttons and LED display, top and bottom operating areas are freely configurable
Equipment	
Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Type of configuration	Laserdruck
Transmitter duty cycle	1 %
Safety	
REACH conform	No
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	KNX radio- operating systems
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic
Secondary design line(s)	Electronics platform, Berker R.1, Berker R.3, Berker R.8, Series R.classic, Serie 1930