



BD226

## Earth leakage add-on block 2P 25A 30mA AC Class

### Technical properties

#### Architecture

Neutral position	left
Number of poles	2 P

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	30 mA
Rated current	25 A

#### Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

#### Frequency

Frequency	50 Hz
-----------	-------

#### Power

Total power loss under $I_N$	10.9 W
Power loss per pole at $I_N$	5.5 W

#### Tripping

Protected against nuisance tripping	No
Short-time delayed tripping	No

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

#### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	NA
Top removability for modular devices	Yes
Bottom removability for modular devices	No
<b>Connection</b>	
Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>
Type of connection	with screw
<b>Settings</b>	
Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP20
Residual current type	AC
<b>Use conditions</b>	
Operating temperature	-5...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Air humidity protection	Execution I