



85656288



IP20

**KNX radio wall-transm. 2gang flat quickl., S.1/B.3/B.7, p.white, matt, plastic**

**Technical properties**

**Functions**

ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, push-button, status display, dimming value
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

**Connectivity**

Radio protocol	KNX Radio
Receiver category	2

**Dimensions**

Assembling height	14 mm
-------------------	-------

**Frequency**

Radio transmission frequency	868.3 MHz
------------------------------	-----------

**Power**

Radio transmission power	< 10 mW
--------------------------	---------

**Battery**

Battery service life [years]	≈ 5
------------------------------	-----

**Materials**

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt

**Equipment**

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Transmitter duty cycle	1 %

**Safety**

Protection	with dismantling protection
------------	-----------------------------

**Use conditions**

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

**Identification**

Application, usage	KNX radio- operating systems
--------------------	------------------------------

