



85745277



IP20

## KNX radio timer quicklink, display, K.5, al., matt, lacq.

### Technical properties

#### Functions

Astronomic time shift	± 2 h
Random number generator	± 15 mn
ETS additional functions	ETS additional functions: +6 scenes, operating mode on/off, scene loading, time dimming value, push-button, status display
Function	with keylock
Quicklink functions	quicklink functions: switching, 2 scenes, time switching, NO contact push-button, forced control
Slide switch	with switchover manual/automatic mode
Power reserve	≈ 8 h

#### Connectivity

Radio protocol	KNX Radio
----------------	-----------

#### Dimensions

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

#### Power

Radio transmission power	< 10 mW
--------------------------	---------

#### Measurement

Running accuracy	± 3 min/year
------------------	--------------

#### Battery

Power reserve [years]	0 a
-----------------------	-----

#### Materials

Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

#### Settings

Time	with automatic summer-/winter time switching (can be switched off)
------	--

#### Equipment

Number of radio channels	1
Number of quicklink links	max. 20 transmitter/receiver
Number of switching times for on/off	20

#### Use

Differentiation characteristic 2 - Sales	with display
--	--------------

**Safety**

---

Protection index IP	IP20
---------------------	------

---

Protection	with dismantling protection
------------	-----------------------------

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Relative humidity (without condensation)	0...65 % (without condensation)
--	---------------------------------

**Identification**

---

Application, usage	Light control, KNX radio- operating systems
--------------------	---

---

Main design line	Berker K.5
------------------	------------

---

Secondary design line(s)	Berker K.5
--------------------------	------------