



BDH280E

Earth leakage add-on-block 2P 125A 30mA type HI

Technical properties

Architecture

Number of poles	2 P
-----------------	-----

Configuration

Number of modules	6
-------------------	---

Connectivity

Bottom connection alignment for modular devices	Aligned terminal
---	------------------

Main electrical features

Rated operational voltage Ue	240 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

Electric current

Rated residual operating current	30 mA
Rated current	125 A

Electric current / temperature

Rating current 20°C	125 A
Rating current 30°C	125 A
Rating current 40°C	118.9 A
Rating current 50°C	112.4 A
Rating current 60°C	105.6 A
Rating current 70°C	99.4 A

Dimensions

Depth of installed product	69 mm
Height of installed product	103 mm
Width of installed product	160 mm

Power

Total power loss under IN	7.5 W
---------------------------	-------

Tripping

Protected against nuisance tripping	Yes
-------------------------------------	-----

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	7000
Installation, mounting	
Tightening torque	3,5Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	metallic
Type of Bottom Connection for modular devices	with screw
Top removability for modular devices	No
Bottom removability for modular devices	Yes
Settings	
Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s
Standards	
Standard text	IEC 61009-1, EN 61009-1
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Residual current type	A HI
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Air humidity protection	for all climates