



BD325



## Earth leakage add-on block 3P 25A 30mA A high immunity Class

### Technical properties

#### Architecture

Neutral position	left
Number of poles	3 P

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	30 mA
Rated current	25 A

#### Electric current / temperature

Rating current 40°C	25 A
---------------------	------

#### Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

#### Frequency

Frequency	50 Hz
-----------	-------

#### Power

Total power loss under IN	4.4 W
---------------------------	-------

#### Tripping

Protected against nuisance tripping	Yes
Short-time delayed tripping	Yes

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

#### Installation, mounting

Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	NA
Top removability for modular devices	No
Bottom removability for modular devices	Yes

### Settings

Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s

### Standards

Standard text	EN 61009-2-1 ; EN 62423
European directive WEEE	concerned

### Safety

Protection index IP	IP20
Residual current type	A HI

### Use conditions

Operating temperature	-5...40 °C
Altitude	2000 m