



BD326



Earth leakage add-on block 3P 25A 30mA AC Class

Technical properties

Architecture

Neutral position	left
Number of poles	3 P

Configuration

Number of modules	2
-------------------	---

Main electrical features

Rated operational voltage U_e	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
Rated current	25 A

Electric current / temperature

Rating current 40°C	25 A
---------------------	------

Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

Frequency

Frequency	50 Hz
-----------	-------

Power

Total power loss under I_N	16.7 W
Power loss per pole at I_N	5.7 W

Tripping

Protected against nuisance tripping	No
Short-time delayed tripping	No

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Installation, mounting

Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	NA
Top removability for modular devices	Yes
Bottom removability for modular devices	No

Settings

Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
Residual current type	AC

Use conditions

Operating temperature	-5...40 °C
Altitude	2000 m