


BD426



Earth leakage add-on block 4P 25A 30mA AC Class

Technical properties

Architecture

Neutral position	left
Number of poles	4 P

Configuration

Number of modules	2
-------------------	---

Main electrical features

Rated operational voltage U _e	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	30 mA
Rated current	25 A

Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

Frequency

Frequency	50 Hz
-----------	-------

Power

Total power loss under I _N	35.9 W
Power loss per pole at I _n	5.7 W

Tripping

Protected against nuisance tripping	No
Short-time delayed tripping	No

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	NA
Top removability for modular devices	Yes
Bottom removability for modular devices	No
Connection	
Connection cross-sect. flexible conductor	6mm ²
Connection cross-sect. rigid cable	10mm ²
Settings	
Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s
Safety	
Residual current type	AC
Use conditions	
Operating temperature	-5...40 °C
Altitude	2000 m
Air humidity protection	Execution I