



BF440

Earth leakage add-on block 4P 40A 300mA A high immunity Class

Technical properties

Architecture

Neutral position	left
Number of poles	4 P

Configuration

Number of modules	3
-------------------	---

Main electrical features

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

Electric current

Rated residual operating current	300 mA
Rated current	40 A

Electric current / temperature

Rating current 40°C	40 A
---------------------	------

Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

Frequency

Frequency	50 Hz
-----------	-------

Tripping

Protected against nuisance tripping	Yes
-------------------------------------	-----

Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

Installation, mounting

Tightening torque	2,8Nm
Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	NA

Top removability for modular devices	Yes
Bottom removability for modular devices	No
Connection	
Connection cross-sect. flexible conductor	16mm ²
Connection cross-sect. rigid cable	25mm ²
Settings	
Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Residual current type	A HI
Use conditions	
Operating temperature	-5...40 °C
Altitude	2000 m
Air humidity protection	Execution I