



BG264N

**Earth leakage add-on block 2P 63A 500mA AC Class**

**Technical properties**

**Architecture**

Neutral position	right
Number of poles	2 P

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

**Electric current**

Rated residual operating current	500 mA
Rated current	63 A

**Electric current / temperature**

Rating current 40°C	63 A
---------------------	------

**Dimensions**

Depth of installed product	9.2 cm
Height of installed product	3.5 cm
Width of installed product	7 cm

**Frequency**

Frequency	50 Hz
-----------	-------

**Tripping**

Protected against nuisance tripping	No
Short-time delayed tripping	No

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

**Installation, mounting**

Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	NA

Top removability for modular devices	Yes
Bottom removability for modular devices	No
<b>Connection</b>	
Connection cross-sect. flexible conductor	16mm <sup>2</sup>
<b>Settings</b>	
Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP20
Residual current type	AC
<b>Use conditions</b>	
Operating temperature	-5...40 °C
Altitude	2000 m