


BF426



## Earth leakage add-on block 4P 25A 300mA AC Class

### Technical properties

#### Architecture

Neutral position	left
Number of poles	4 P

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage $U_e$	230 / 400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V

#### Electric current

Rated residual operating current	300 mA
Rated current	25 A

#### Dimensions

Depth of installed product	9.2 cm
Height of installed product	7 cm
Width of installed product	3.5 cm

#### Frequency

Frequency	50 Hz
-----------	-------

#### Power

Total power loss under $I_N$	30.6 W
Power loss per pole at $I_n$	4.9 W

#### Tripping

Protected against nuisance tripping	No
Short-time delayed tripping	No

#### Endurance

Electric endurance in number of cycles	2000
Number of mechanical operations	2000

#### Installation, mounting

Tightening torque	1,7Nm
-------------------	-------

Type of top rail clip for modular devices	Plastic
Type of bottom rail clip for modular devices	NA
Top removability for modular devices	Yes
Bottom removability for modular devices	No
<b>Connection</b>	
Connection cross-sect. flexible conductor	6mm <sup>2</sup>
Connection cross-sect. rigid cable	10mm <sup>2</sup>
<b>Settings</b>	
Rated fault current adjustable	No
Delay adjustable	No
Time delay of residual current	0 s
<b>Safety</b>	
Residual current type	AC
<b>Use conditions</b>	
Operating temperature	-5...40 °C
Altitude	2000 m
Air humidity protection	Execution I